

SealerSales W-300A 12" Automatic Impulse Sealer w/ 2.7mm Seal Width

Product Spec Sheet



Provided by

MyBinding.com

When Image Matters.

Call Us at 1-800-944-4573

W-Series Automatic SEALERS

FEATURES

- Automatic impulse sealing with precise electronic control
- Dual mode operation: automatic or manual
- Foot switch allows both hands to be free
- 3 separate control settings for sealing time, recycle time, and congealing time
- Includes electric foot switch and worktable

W-Series automatic sealers are designed for the continuous sealing of thermoplastic materials. Depending on the model of the sealer, materials up to 24" wide and 15mil total thickness can be sealed. Seal widths of 2.7mm and 5mm are available. Unit is controlled by a plug-in transistorized circuit board. Equipped with an electronic timer and electromagnet, once correct settings have been established, consistent seals will be maintained automatically.



We now have a new 10mm model

MODEL #	SEAL LENGTH	SEAL WIDTH	POWER	WEIGHT (LBS)	DIMENSIONS
W-300A W-305A W-3010A	12"	2.7MM 5MM 10MM	450W 600W 1000W	50 52 55	17.3" X 14.2" X 7.9"
W-450A W-455A W-4510A	18"	2.7MM 5MM 10MM	600W 800W TBD	56 59 TBD	20.9" X 14.2" X 7.9"
W-600A W-605A W-6010A	24"	2.7MM 5MM 10MM	800W 1300W TBD	68 70 TBD	26.8" X 14.2" X 7.9"
W-755AA	30"	5MM	1200W	82	32.7" X 14.4" X 9.8"

We also carry double automatic impulse sealers which can seal up to 24mil total thickness. Double impulse sealers use two heating elements (upper and lower) to fuse materials from both sides at the same time allowing thicker materials to be sealed.



MODEL #	SEAL LENGTH	SEAL WIDTH	POWER	WEIGHT (LBS)	DIMENSIONS
W-305AT	12"	5MM	1210W	54	17.3" X 14.2" X 7.9"
W-455AT	18"	5MM	2640W	62	20.9" X 14.2" X 7.9"

EASY TO OPERATE

For **automatic operation**, set the control on auto. Adjust the sealing time (heating time), congealing time (cooling time), and recycle time (automatic operation of jaws). Insert material to be sealed and when jaw opens, remove sealed material. For **manual operation**, set the control to manual. Insert the material to be sealed. Press down on the foot switch to activate the sealing bar.